



EU300

control relay triphased phase 400V

Technical characteristics

Configuration

Number of modules	2
-------------------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Acceptable current rating with AC1	8 A
------------------------------------	-----

Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Length	64 mm
Width of installed product	35 mm

Power

Total power loss under IN	4 W
---------------------------	-----

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Type of contacts	1 changeover
------------------	--------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...55 °C
Storage/transport temperature	-40...70 °C