



FL112A

**Steel enclosure, Orion.Plus, plain door 500x400x200 mm**

**Technical characteristics**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Configuration**

Number of modules	48
-------------------	----

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Insertion depth	200 mm
Depth of installed product	200 mm
Internal depth	200 mm
Height of installed product	500 mm
Width of installed product	400 mm
Width in division units	16
Thickness of sidewall material	2 mm

**Cover, door**

Type of door closing	lock with male triangular wrench
Interlockable	Yes
Number of keylock of the door	1
Cover type	Closed (plain)
Door leave	single
Cover type	Cover
Transparent cover or door	No

**Materials**

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Settings**

Enclosure type	Wall cabinet
----------------	--------------

**Equipment**

Number of rows	3
Number of keys	1
Number of openings for flange plates	2
Extension possible	No

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection class	isol.class I
Fire resistance	-