



FL126A

Steel enclosure, Orion.Plus, plain door 950x600x300 mm

Technical characteristics

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	156
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Depth of installed product	300 mm
Internal depth	295 mm
Height of installed product	950 mm
Width of installed product	600 mm
Width in division units	26
Thickness of sidewall material	2 mm

Cover, door

Material thickness cover	21.5 mm
Type of door closing	lock with male triangular wrench
Interlockable	Yes
Number of keylock of the door	2
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Subject to technical modifications

Number of rows	6
Number of keys	2
Number of openings for flange plates	2
Extension possible	Yes
Standards	
European directive WEEE	concerned
Safety	
IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Fire resistance	-