



FL128A

**Steel enclosure, Orion.Plus, plain door 950x800x300 mm**

**Technical characteristics**

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 222

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Depth of installed product 300 mm

Internal depth 300 mm

Height of installed product 950 mm

Width of installed product 800 mm

Width in division units 37

Thickness of sidewall material 2 mm

**Cover, door**

Interlockable Yes

Number of keylock of the door 2

Cover type Closed (plain)

Door leave single

Cover type Cover

Transparent cover or door No

**Materials**

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment powder-coated

**Installation, mounting**

Suitable for outdoor use No

**Settings**

Enclosure type Wall cabinet

**Equipment**

Number of rows 6

Number of keys	2
Number of openings for flange plates	2
Extension possible	Yes
<b>Safety</b>	
IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	Yes
Fire resistance	-