



FL229B

**Polyester enclosure, Orion.Plus, plain door 800x600x300 mm**

**Technical characteristics**

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 140

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Depth of installed product 300 mm

Internal depth 300 mm

Height of installed product 800 mm

Width of installed product 600 mm

Width in division units 28

Thickness of sidewall material 2 mm

**Cover, door**

Type of door closing lock with male triangular wrench

Interlockable Yes

Number of keylock of the door 2

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material glas reinforced polyester

Type of surface treatment untreated

**Installation, mounting**

Suitable for outdoor use Yes

**Settings**

Enclosure type Wall cabinet

**Equipment**

---

Number of rows	4
Number of keys	2
Quantity of rails	5
Number of openings for flange plates	0

---

**Standards**

---

European directive WEEE	concerned
-------------------------	-----------

---

**Safety**

---

Protection index IP	IP66
Protection class	isol.class II

---