



FL368B

Polyester double enclosure, Orion.Plus, plain door 2050x1100x300 mm

Technical characteristics

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	230
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	300 mm
Depth of installed product	300 mm
Internal depth	300 mm
Height of installed product	2050 mm
Width of installed product	1100 mm
Thickness of sidewall material	2 mm

Cover, door

Material thickness cover	2 mm
Type of door closing	Barrel lock
Interlockable	Yes
Cover type	Closed (plain)
Door leave	single
Transparent cover or door	No

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	glas reeinforced polyester
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Equipment

Number of rows	5
Quantity of section in width	2

Subject to technical modifications

Number of keys	2
Number of openings for flange plates	0
Extension possible	No
Standards	
European directive WEEE	not concerned
Safety	
Protection class	isol.class II
REACH conform	No
Fire resistance	-