



FM307

**Floor standing steel enclosure, Quadro5, 1710x900x260 mm**

**Technical characteristics**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Configuration**

Number of modules	360
-------------------	-----

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Insertion depth	260 mm
Depth of installed product	260 mm
Internal depth	260 mm
Height of installed product	1710 mm
Width of installed product	900 mm
Width in division units	36
Thickness of sidewall material	2 mm

**Cover, door**

Material thickness cover	2 mm
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel
Type of surface treatment	powder-coated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Equipment**

Number of rows	11
Quantity of section in width	3

Subject to technical modifications

Number of openings for flange plates	2
Extension possible	Yes
<b>Standards</b>	
European directive WEEE	concerned
<b>Safety</b>	
IK protection code against mechanical impacts	IK10
Protection index IP	IP55
REACH conform	No
Fire resistance	-