



FU22DN

**Enclosure, NewVegaD, 537x550x150mm, 48 modules, flush-mounted, distribution**

**Technical characteristics**

**Configuration**

Module	with terminals
Number of modules	48

**Electric current**

Rated current	160 A
---------------	-------

**Dimensions**

Insertion depth	110 mm
Depth of installed product	150 mm
Internal depth	110 mm
Height of installed product	537 mm
Installation height	537 mm
Width of installed product	600 mm
Width in division units	24
Thickness of sidewall material	1 mm
Built-in width	550 mm

**Cover, door**

Cover type	With Notch
Door locking	without
Door leave	single
Cover type	none / closed
Transparent cover or door	No

**Materials**

Colour	white
RAL colour	RAL 9010 - Pure white
Type of surface treatment	powder-coated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Connection**

Number of conduit inlets	4
--------------------------	---

**Settings**

Enclosure type	Distributor empty cabinet
----------------	---------------------------

**Equipment**

Number of rows	2
----------------	---

Quantity of section in width	2
Quantity of rails	2
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	No

### Standards

European directive WEEE	not concerned
-------------------------	---------------

### Safety

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No