



FU22DN

**Enclosure, NewVegaD, 537x550x150mm, 48 modules, flush-mounted, distribution**

**Technical characteristics**

**Architecture**

Fixing mode flush-mounting

**Configuration**

Module with terminals

Number of modules 48

**Electric current**

Rated current 160 A

**Dimensions**

Insertion depth 110 mm

Depth of installed product 150 mm

Internal depth 110 mm

Height of installed product 537 mm

Installation height 537 mm

Width of installed product 600 mm

Width in division units 24

Thickness of sidewall material 1 mm

Built-in width 550 mm

**Cover, door**

Cover type With Notch

Door locking without

Door leave single

Cover type none / closed

Transparent cover or door No

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Material Plastic/metal

Type of surface treatment powder-coated

**Installation, mounting**

Suitable for outdoor use No

**Connection**

Number of conduit inlets 4

**Settings**

Subject to technical modifications

**Equipment**

---

Number of rows	2
Quantity of section in width	2
Quantity of rails	2
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	No

**Standards**

---

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

---

IK protection code against mechanical impacts	IK07
Protection index IP	IP30
Protection class	isol.class II