



GTVBS25

## Double switch socket for BS box

### Technical characteristics

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Functions

Overvoltage protection	No
------------------------	----

#### Configuration

Number of modules	0
-------------------	---

#### Main electrical features

Nominal voltage	250 V AC
Rated voltage	220...230 V AC
Rated current	13 A

#### Electric current

Rated current	13 A
---------------	------

#### Dimensions

Depth	53.2 mm
Height	86 mm
Width	146 mm

#### Cover, door

Cover	Full cover plate
-------	------------------

#### Power supply

Special power supply	No special power supply
----------------------	-------------------------

#### Materials

Colour of design line	grey
Colour independent of design lines	Grey
Colour	grey
Material	Steel

#### Installation, mounting

Fixing type	With screws
Installation mode	for flush-mounted and hollow-wall mounting, for screw fastening

#### Connection

Type of connection	screw
--------------------	-------

**Equipment**

Number of socket outlets switchable	0
-------------------------------------	---

**Safety**

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection