



GTVBS25

Double switch socket for BS box

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

Overtoltage protection No

Configuration

Number of modules 0

Main electrical features

Nominal voltage 250 V AC

Rated voltage 220...230 V AC

Rated current 13 A

Electric current

Rated current 13 A

Dimensions

Depth 53.2 mm

Height 86 mm

Width 146 mm

Cover, door

Cover Full cover plate

Power supply

Special power supply No special power supply

Materials

Colour of design line grey

Colour independent of design lines Grey

Colour grey

Material Steel

Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting, for screw fastening

Connection

Type of connection screw

Equipment

Safety

Protection index IP

IP20

Protection

Enhanced contact protection