



GTVBS25

## Double switch socket for BS box

### Technical characteristics

#### Functions

Overvoltage protection No

#### Configuration

Number of modules 0

#### Main electrical features

Nominal voltage 250 V AC

Rated voltage 220...230 V AC

Rated current 13 A

#### Electric current

Rated current 13 A

#### Dimensions

Depth 53.2 mm

Height 86 mm

Width 146 mm

#### Cover, door

Cover Full cover plate

#### Power supply

Special power supply No special power supply

#### Materials

Colour of design line grey

Colour independent of design lines Grey

Surface appearance glossy

#### Installation, mounting

Fixing type With screws

Installation mode for flush-mounted and hollow-wall mounting ; for screw fastening

#### Connection

Type of connection screw

#### Cable

Wiring with double earth connection

#### Scope of delivery

Component

**Equipment**

---

Number of socket outlets switchable 0

**Safety**

---

IK protection code against mechanical impacts sonstige

---

REACH conform Yes

---

RoHS conform Yes

---

Halogen free No

---

Protection Enhanced contact protection