



GTVBS25

Double switch socket for BS box

Technical characteristics

Functions

Overvoltage protection No

Configuration

Number of modules 0

Main electrical features

Nominal voltage 250 V AC

Rated voltage 220...230 V AC

Rated current 13 A

Electric current

Rated current 13 A

Dimensions

Depth 53.2 mm

Height 86 mm

Width 146 mm

Cover, door

Cover Full cover plate

Power supply

Special power supply No special power supply

Materials

Colour of design line grey

Colour independent of design lines Grey

Surface appearance glossy

Installation, mounting

Fixing type With screws

Installation mode for flush-mounted and hollow-wall mounting ; for screw fastening

Connection

Type of connection screw

Cable

Wiring with double earth connection

Scope of delivery

Component

with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each

Equipment

Number of socket outlets switchable 0

Safety

IK protection code against mechanical impacts sonstige

REACH conform Yes

RoHS conform Yes

Halogen free No

Protection Enhanced contact protection