



HTC310H

**COMMUNICATION Module without inputs and outputs**

**Technical characteristics**

**Configuration**

Number of modules	2
-------------------	---

**Main electrical features**

Type of supply voltage	DC
------------------------	----

**Voltage**

Operating voltage	24 V DC
-------------------	---------

**Standards**

European directive RoHs	compliant
-------------------------	-----------

**Safety**

REACH conform	No
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-25...70 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Storage/transport temperature	-35...70 °C