



HTC310H

## COMMUNICATION Module without inputs and outputs

### Technical characteristics

#### Architecture

Fixing mode DIN rail type O (symmetrical)

#### Configuration

Number of modules 2

#### Voltage

Operating voltage 24 V DC

#### Standards

European directive RoHS compliant

European directive WEEE concerned

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -25...70 °C

Storage/transport temperature -35...70 °C