



HTC320H

COMMUNICATION Module with inputs and outputs

Technical characteristics

Configuration

Number of modules	2
-------------------	---

Main electrical features

Type of supply voltage	DC
------------------------	----

Voltage

Input voltage	24 V DC
Operating voltage	24 V DC
Output voltage	24...48 V DC

Electric current

Input current	max. 15 mA
Output current	max. 50 mA

Equipment

Number of digital inputs	2
--------------------------	---

Standards

European directive RoHs	compliant
-------------------------	-----------

Use conditions

Operating temperature	-25...70 °C
Storage/transport temperature	-35...70 °C