



HTC320H

COMMUNICATION Module with inputs and outputs

Technical characteristics

Architecture

Fixing mode	DIN rail type O (symmetrical)
-------------	-------------------------------

Configuration

Number of modules	2
-------------------	---

Voltage

Input voltage	24 V DC
Operating voltage	24 V DC
Output voltage	24...48 V DC

Electric current

Input current	max. 15 mA
Output current	max. 50 mA

Equipment

Number of digital inputs	2
--------------------------	---

Standards

European directive RoHS	compliant
European directive WEEE	concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...70 °C
Storage/transport temperature	-35...70 °C