



HXA024H

Alarm contact 1NO+1NC 250V AC (x160-P160-x250-P250-x630-P630)

Technical characteristics

Main electrical features

Rated operational voltage Ue	250 V
Type of supply voltage	AC/DC

Voltage

Rated impulse withstand voltage	1500 V
Rated operational voltage in DC	125 V

Electric current

Rated current	3 A
---------------	-----

Power

Total power loss under IN	3 W
---------------------------	-----

Connection

Type of contacts	1 NO/NC
Type of connection	quick connect

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	1
Number of auxiliary contacts as fault signal	2

Standards

European directive RoHS	voluntary compliance
European directive WEEE	concerned

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes