



HXA028H

Alarm contact-Low level NO-NC right side (x630/P630)

Technical characteristics

Architecture

Fixing mode	Clipped
-------------	---------

Main electrical features

Rated operational voltage Ue	125 V
Type of supply voltage	AC/DC

Voltage

Rated impulse withstand voltage	1500 V
Rated operational voltage in DC	30 V

Electric current

Rated current	0.1 A
---------------	-------

Power

Total power loss under IN	3 W
---------------------------	-----

Connection

Type of contacts	1 changeover
Type of connection	quick connect

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	1
Number of auxiliary contacts as fault signal	2

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------