



HXA028H

Alarm contact-Low level NO-NC right side (x630/P630)

Technical characteristics

Architecture

Fixing mode Clipped

Main electrical features

Rated operational voltage Ue 125 V

Type of supply voltage AC/DC

Voltage

Rated impulse withstand voltage 1500 V

Rated operational voltage in DC 30 V

Electric current

Rated current 0.1 A

Power

Total power loss under IN 3 W

Connection

Type of contacts 1 changeover

Type of connection quick connect

Equipment

Number of auxiliary contacts as normally closed contact 0

Number of auxiliary contacts as normally open contact 0

Number of auxiliary contacts as change-over contact 1

Number of auxiliary contacts as fault signal 2

Standards

European directive RoHS voluntary compliance