



HXB042H

**Motor operator x250 230-240VAC**

**Technical characteristics**

**Architecture**

Type of order motor drive

**Main electrical features**

Rated operational voltage Ue 220 / 240 V

Type of supply voltage AC

Frequency 50/60 Hz

**Voltage**

DC control voltage 0 V

Command voltage AC 230 / 240 V

Rated operational voltage in DC 0 V

**Frequency**

Frequency 50 to 60 Hz

**Power**

Total power loss under IN 24 W

**Standards**

European directive RoHS voluntary compliance

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m