



HXC011H

Undervoltage Release 24V DC (h250-h400-h630)

Technical characteristics

Voltage

| | |
|--------------------|------|
| DC control voltage | 24 V |
| Command voltage AC | 0 V |

Frequency

| | |
|-----------|------|
| Frequency | 0 Hz |
|-----------|------|

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 0.6 W |
|---------------------------|-------|

Equipment

| | |
|---|---|
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact | 0 |
| Number of auxiliary contacts as change-over contact | 0 |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Use conditions

| | |
|--|--------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
| Altitude | 2000 m |