



HXC014H

Undervoltage Release 200-240V AC (h250-h400-h630)

Technical characteristics

Voltage

| | |
|--------------------|-------------|
| DC control voltage | 0 V |
| Command voltage AC | 200 / 240 V |

Frequency

| | |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 2.8 W |
|---------------------------|-------|

Equipment

| | |
|---|---|
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact | 0 |
| Number of auxiliary contacts as change-over contact | 0 |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP4X |
|---------------------|------|

Use conditions

| | |
|--|--------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
| Altitude | 2000 m |