



HXE042H

## Motor operator H800-H1000 100-240VAC

### Technical characteristics

#### Architecture

Type of order	motor drive
---------------	-------------

#### Main electrical features

Rated operational voltage Ue	100 / 240 V
------------------------------	-------------

Type of supply voltage	AC
------------------------	----

Frequency	50/60 Hz
-----------	----------

#### Voltage

DC control voltage	0 V
--------------------	-----

Command voltage AC	100 / 240 V
--------------------	-------------

Rated operational voltage in DC	0 V
---------------------------------	-----

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Total power loss under IN	24 W
---------------------------	------

#### Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
--	---

Altitude	2000 m
----------	--------