



HXE042H

**Motor operator H800-H1000 100-240VAC**

**Technical characteristics**

**Main electrical features**

|                              |             |
|------------------------------|-------------|
| Rated operational voltage Ue | 100 / 240 V |
| Type of supply voltage       | AC          |
| Frequency                    | 50/60 Hz    |

**Voltage**

|                                 |             |
|---------------------------------|-------------|
| DC control voltage              | 0 V         |
| Command voltage AC              | 100 / 240 V |
| Rated operational voltage in DC | 0 V         |

**Frequency**

|           |             |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

**Power**

|                           |      |
|---------------------------|------|
| Total power loss under IN | 24 W |
|---------------------------|------|

**Standards**

|                         |                      |
|-------------------------|----------------------|
| European directive RoHS | voluntary compliance |
| European directive WEEE | concerned            |

**Use conditions**

|  |        |
|--|--------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3      |
| Altitude   | 2000 m |