



HXT042H

## Motor Operator P250 230-240VAC with Auto-Reset

### Technical characteristics

#### Architecture

Type of order motor drive

#### Main electrical features

Type of supply voltage AC

#### Voltage

DC control voltage 0 V

Command voltage AC 230 / 240 V

#### Electric current

Inrush current OFF-RESET 230-240V AC - 6A

Inrush current ON 230-240V AC - 6A

Operating current OFF-RESET 230-240V AC - 3.4A

Operating current ON 230-240V AC - 3.4A

#### Frequency

Frequency 50 to 60 Hz

#### Standards

European directive RoHS compliant

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

#### Use conditions

Altitude 2000 m