



HXT044H

Motor Operator P250 230-240VAC without Auto-Reset

Technical characteristics

Architecture

Type of order	motor drive
---------------	-------------

Main electrical features

Type of supply voltage	AC
------------------------	----

Voltage

DC control voltage	0 V
--------------------	-----

Command voltage AC	230 / 240 V
--------------------	-------------

Electric current

Inrush current OFF-RESET	230-240V AC - 6A
--------------------------	------------------

Inrush current ON	230-240V AC - 6A
-------------------	------------------

Operating current OFF-RESET	230-240V AC - 3.4A
-----------------------------	--------------------

Operating current ON	230-240V AC - 3.4A
----------------------	--------------------

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Altitude	2000 m
----------	--------