



HXT046HK

Motor Operator P250 100-110VAC/DC without Auto-Reset + key

Technical characteristics

Architecture

Type of order motor drive

Main electrical features

Type of supply voltage AC/DC

Voltage

DC control voltage 100 / 110 V

Command voltage AC 100 / 110 V

Electric current

Inrush current OFF-RESET 110V AC - 8.7A ; 110V DC - 7.6A

Inrush current ON 110V AC - 8.7A ; 110V DC - 7.6A

Operating current OFF-RESET 110V AC - 3.6A ; 110V DC - 3.4A

Operating current ON 110V AC - 3.6A ; 110V DC - 3.4A

Frequency

Frequency 50 to 60 Hz

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Altitude 2000 m