



HXT046HK

**Motor Operator P250 100-110VAC/DC without Auto-Reset + key**

**Technical characteristics**

**Architecture**

Type of order motor drive

**Main electrical features**

Type of supply voltage AC/DC

**Voltage**

DC control voltage 100 / 110 V

Command voltage AC 100 / 110 V

**Electric current**

Inrush current OFF-RESET 110V AC - 8.7A ; 110V DC - 7.6A

Inrush current ON 110V AC - 8.7A ; 110V DC - 7.6A

Operating current OFF-RESET 110V AC - 3.6A ; 110V DC - 3.4A

Operating current ON 110V AC - 3.6A ; 110V DC - 3.4A

**Frequency**

Frequency 50 to 60 Hz

**Standards**

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

**Use conditions**

Altitude 2000 m