



HXT049HK

Motor Operator P250 48VDC without Auto-Reset +key

Technical characteristics

Architecture

Type of order	motor drive
---------------	-------------

Main electrical features

Type of supply voltage	DC
------------------------	----

Voltage

DC control voltage	48 V
Command voltage AC	0 V

Electric current

Inrush current OFF-RESET	48V DC - 17A
Inrush current ON	48V DC - 12A
Operating current OFF-RESET	48V DC - 12A
Operating current ON	48V DC - 12A

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Altitude	2000 m
----------	--------