



HXW040HK

Motor Operator x630/P630 24-48VDC with Auto-Reset + key

Technical characteristics

Architecture

Type of order motor drive

Main electrical features

Type of supply voltage DC

Voltage

DC control voltage 24 / 48 V

Command voltage AC 0 V

Electric current

Inrush current OFF-RESET 24V DC - 15.3A ; 48V DC - 7.4A

Inrush current ON 24V DC - 12A ; 48V DC - 12A

Operating current OFF-RESET 24V DC - 6.7A ; 48V DC - 3.5A

Power

Total power loss under IN 0 W

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Altitude 2000 m