



HXW041H

Motor Operator x630/P630 100-120VDC with Auto-Reset

Technical characteristics

Architecture

Type of order	motor drive
---------------	-------------

Main electrical features

Type of supply voltage	DC
------------------------	----

Voltage

DC control voltage	100 / 120 V
--------------------	-------------

Command voltage AC	0 V
--------------------	-----

Electric current

Inrush current OFF-RESET	100-120V DC - 4.4A
--------------------------	--------------------

Inrush current ON	100-120V DC - 4.1A
-------------------	--------------------

Operating current OFF-RESET	100-120V DC - 1.4A
-----------------------------	--------------------

Power

Total power loss under IN	0 W
---------------------------	-----

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Altitude	2000 m
----------	--------