



HXW041H

**Motor Operator x630/P630 100-120VDC with Auto-Reset**

**Technical characteristics**

**Architecture**

Type of order motor drive

**Main electrical features**

Type of supply voltage DC

**Voltage**

DC control voltage 100 / 120 V

Command voltage AC 0 V

**Electric current**

Inrush current OFF-RESET 100-120V DC - 4.4A

Inrush current ON 100-120V DC - 4.1A

Operating current OFF-RESET 100-120V DC - 1.4A

**Power**

Total power loss under IN 0 W

**Standards**

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

**Use conditions**

Altitude 2000 m