



HXW041HK

## Motor Operator x630/P630 100-120VDC with Auto-Reset + key

### Technical characteristics

#### Architecture

Type of order	motor drive
---------------	-------------

#### Main electrical features

Type of supply voltage	DC
------------------------	----

#### Voltage

DC control voltage	100 / 120 V
Command voltage AC	0 V

#### Electric current

Inrush current OFF-RESET	100-120V DC - 4.4A
Inrush current ON	100-120V DC - 4.1A
Operating current OFF-RESET	100-120V DC - 1.4A

#### Power

Total power loss under IN	0 W
---------------------------	-----

#### Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

#### Use conditions

Altitude	2000 m
----------	--------