



HXW042H

## Motor Operator x630/P630 100-240VAC with Auto-Reset

### Technical characteristics

#### Architecture

Type of order motor drive

#### Main electrical features

Type of supply voltage AC

#### Voltage

DC control voltage 0 V

Command voltage AC 100 / 240 V

#### Electric current

Inrush current OFF-RESET 100-110V AC - 4.2A ; 200-220V AC - 4.2A ; 230-240V AC - 4.2A

Inrush current ON 100-110V AC - 4.1A ; 200-220V AC - 4.1A ; 230-240V AC - 4.1A

Operating current OFF-RESET 100-110V AC - 1.7A ; 200-220V AC - 1.7A ; 230-240V AC - 1.7A

#### Frequency

Frequency 50 to 60 Hz

#### Power

Total power loss under IN 0 W

#### Standards

European directive RoHs voluntary compliance

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

#### Use conditions

Altitude 2000 m