



HXW042H

Motor Operator x630/P630 100-240VAC with Auto-Reset

Technical characteristics

Main electrical features

Type of supply voltage	AC
------------------------	----

Voltage

DC control voltage	0 V
--------------------	-----

Command voltage AC	100 / 240 V
--------------------	-------------

Electric current

Inrush current OFF-RESET	100-110V AC - 4.2A ; 200-220V AC - 4.2A ; 230-240V AC - 4.2A
--------------------------	--

Inrush current ON	100-110V AC - 4.1A ; 200-220V AC - 4.1A ; 230-240V AC - 4.1A
-------------------	--

Operating current OFF-RESET	100-110V AC - 1.7A ; 200-220V AC - 1.7A ; 230-240V AC - 1.7A
-----------------------------	--

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	0 W
---------------------------	-----

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Altitude	2000 m
----------	--------