



HXW042HK

Motor Operator x630/P630 100-240VAC with Auto-Reset + key

Technical characteristics

Architecture

Type of order motor drive

Main electrical features

Type of supply voltage AC

Voltage

DC control voltage 0 V

Command voltage AC 100 / 240 V

Electric current

Inrush current OFF-RESET 100-110V AC - 4.2A ; 200-220V AC - 4.2A ; 230-240V AC - 4.2A

Inrush current ON 100-110V AC - 4.1A ; 200-220V AC - 4.1A ; 230-240V AC - 4.1A

Operating current OFF-RESET 100-110V AC - 1.7A ; 200-220V AC - 1.7A ; 230-240V AC - 1.7A

Frequency

Frequency 50 to 60 Hz

Power

Total power loss under IN 0 W

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Altitude 2000 m