



HXW043H

Motor Operator x630/P630 24-48VDC without Auto-Reset

Technical characteristics

Voltage

DC control voltage	24 / 48 V
Command voltage AC	0 V

Electric current

Inrush current OFF-RESET	24V DC - 15.3A ; 48V DC - 7.4A
Inrush current ON	24V DC - 12A ; 48V DC - 12A
Operating current OFF-RESET	24V DC - 6.7A ; 48V DC - 3.5A

Power

Total power loss under IN	0 W
---------------------------	-----

Standards

European directive RoHS	voluntary compliance
European directive WEEE	concerned

Use conditions

Altitude	2000 m
----------	--------