



HXW043H

Motor Operator x630/P630 24-48VDC without Auto-Reset

Technical characteristics

Architecture

| | |
|---------------|-------------|
| Type of order | motor drive |
|---------------|-------------|

Main electrical features

| | |
|------------------------|----|
| Type of supply voltage | DC |
|------------------------|----|

Voltage

| | |
|--------------------|-----------|
| DC control voltage | 24 / 48 V |
|--------------------|-----------|

| | |
|--------------------|-----|
| Command voltage AC | 0 V |
|--------------------|-----|

Electric current

| | |
|--------------------------|--------------------------------|
| Inrush current OFF-RESET | 24V DC - 15.3A ; 48V DC - 7.4A |
|--------------------------|--------------------------------|

| | |
|-------------------|-----------------------------|
| Inrush current ON | 24V DC - 12A ; 48V DC - 12A |
|-------------------|-----------------------------|

| | |
|-----------------------------|-------------------------------|
| Operating current OFF-RESET | 24V DC - 6.7A ; 48V DC - 3.5A |
|-----------------------------|-------------------------------|

Power

| | |
|---------------------------|-----|
| Total power loss under IN | 0 W |
|---------------------------|-----|

Standards

| | |
|-------------------------|----------------------|
| European directive RoHS | voluntary compliance |
|-------------------------|----------------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

| | |
|--------------|----|
| Halogen free | No |
|--------------|----|

Use conditions

| | |
|----------|--------|
| Altitude | 2000 m |
|----------|--------|