



HXW043HK

**Motor Operator x630/P630 24-48VDC without Auto-Reset + key**

**Technical characteristics**

**Architecture**

Type of order motor drive

**Main electrical features**

Type of supply voltage DC

**Voltage**

DC control voltage 24 / 48 V

Command voltage AC 0 V

**Electric current**

Inrush current OFF-RESET 24V DC - 15.3A ; 48V DC - 7.4A

Inrush current ON 24V DC - 12A ; 48V DC - 12A

Operating current OFF-RESET 24V DC - 6.7A ; 48V DC - 3.5A

**Power**

Total power loss under IN 0 W

**Standards**

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

**Use conditions**

Altitude 2000 m