



HXW044H

**Motor Operator x630/P630 100-240VAC without Auto-Reset**

**Technical characteristics**

**Architecture**

Type of order motor drive

**Main electrical features**

Type of supply voltage AC

**Voltage**

DC control voltage 0 V

Command voltage AC 100 / 240 V

**Electric current**

Inrush current OFF-RESET 100-110V AC - 4.2A ; 200-220V AC - 4.2A ; 230-240V AC - 4.2A

Inrush current ON 100-110V AC - 4.1A ; 200-220V AC - 4.1A ; 230-240V AC - 4.1A

Operating current OFF-RESET 100-110V AC - 1.7A ; 200-220V AC - 1.7A ; 230-240V AC - 1.7A

**Frequency**

Frequency 50 to 60 Hz

**Power**

Total power loss under IN 0 W

**Standards**

European directive RoHs voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

**Use conditions**

Altitude 2000 m