



HXW046H

Motor Operator x630/P630 100-120VDC without Auto-Reset

Technical characteristics

Architecture

Type of order motor drive

Main electrical features

Type of supply voltage DC

Voltage

DC control voltage 100 / 120 V

Command voltage AC 0 V

Electric current

Inrush current OFF-RESET 100-120V DC - 4.4A

Inrush current ON 100-120V DC - 4.1A

Operating current OFF-RESET 100-120V DC - 1.4A

Power

Total power loss under IN 0 W

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Altitude 2000 m