



HYB031H

**Rear connection (x/P250-P250) - 3P**

**Technical characteristics**

**Architecture**

|                 |     |
|-----------------|-----|
| Number of poles | 3 P |
|-----------------|-----|

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

**Installation, mounting**

|                   |      |
|-------------------|------|
| Tightening torque | 12Nm |
|-------------------|------|

**Standards**

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |

**Use conditions**

|   |        |
|---|--------|
| Degree of pollution according to IEC 60664 /<br>IEC 60947-2 | 3      |
| Altitude  | 2000 m |