



HYC201H

PM Base Plug In h250 LSI 4P

Technical characteristics

Architecture

| | |
|-----------------|-----|
| Number of poles | 4 P |
|-----------------|-----|

Power

| | |
|---------------------------|--------|
| Total power loss under IN | 38.2 W |
| Power loss per pole at In | 12.7 W |

Tripping

| | |
|----------|-----|
| Tripmode | LSI |
|----------|-----|

Installation, mounting

| | |
|------------------------------|-----|
| Built-in | Yes |
| Suitable for busbar mounting | No |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Use conditions

| | |
|---|--------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
| Altitude | 2000 m |