



HYW001H

**Cage terminal x630/P630 Cu/Al 3P 1x 35-300mm<sup>2</sup>**

**Technical characteristics**

**Architecture**

Number of poles	3 P
Type of pole	3 P

**Electric current**

Rated current	630 A
---------------	-------

**Power**

Total power loss under IN	211.2 W
Power loss per pole at In	70.4 W

**Installation, mounting**

Tightening torque	25Nm
-------------------	------

**Connection**

Conductor cross-section	35...300 mm <sup>2</sup>
-------------------------	--------------------------

**Standards**

European directive RoHS	voluntary compliance
-------------------------	----------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes