



HYW011H

**Spread terminal extension x630/P630 3P (up to 400A)**

**Technical characteristics**

**Architecture**

|                 |     |
|-----------------|-----|
| Number of poles | 3 P |
| Type of pole    | 3 P |

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 400 A |
|---------------|-------|

**Power**

|                                       |        |
|---------------------------------------|--------|
| Total power loss under I <sub>N</sub> | 13.8 W |
| Power loss per pole at I <sub>N</sub> | 4.6 W  |

**Standards**

|                         |                      |
|-------------------------|----------------------|
| European directive RoHS | voluntary compliance |
| European directive WEEE | concerned            |