



HYW012H

**Spread terminal extension x630/P630 4P (up to 400A)**

**Technical characteristics**

**Architecture**

|                 |     |
|-----------------|-----|
| Number of poles | 4 P |
| Type of pole    | 4 P |

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 400 A |
|---------------|-------|

**Power**

|                           |        |
|---------------------------|--------|
| Total power loss under IN | 13.8 W |
| Power loss per pole at In | 4.6 W  |

**Installation, mounting**

|                   |      |
|-------------------|------|
| Tightening torque | 18Nm |
|-------------------|------|

**Standards**

|                         |                      |
|-------------------------|----------------------|
| European directive RoHs | voluntary compliance |
|-------------------------|----------------------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | Yes |