



HYW013H

Straight terminal extension x630/P630 4P (up to 630A)

Technical characteristics

Architecture

Number of poles	4 P
Type of pole	4 P

Electric current

Rated current	630 A
---------------	-------

Power

Total power loss under IN	16.7 W
Power loss per pole at In	5.56 W

Installation, mounting

Tightening torque	18Nm
-------------------	------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes