



JK1B10S2

**125A TPN BOARD, INVICTA, 10WAY, SURFACE, FOR 50 OC TESTING**

**Technical characteristics**

**Configuration**

Number of modules 0

**Compatibility**

Suitable for lightning protection No

**Dimensions**

Insertion depth 120 mm

Depth of installed product 125 mm

Internal depth 117 mm

Height of installed product 660 mm

Width of installed product 445 mm

Thickness of sidewall material 1.2 mm

**Cover, door**

Material thickness cover 1.2 mm

Type of door closing non keylock

Identification of protection index 41

Interlockable No

Door locking with special tool

Transparent cover or door No

**Materials**

Colour light grey

**Installation, mounting**

Suitable for outdoor use No

**Connection**

Number of conduit inlets 26

Number of accessible phases 3

**Equipment**

With energy meter No

Quantity of rails 0

Can be accessorized Yes

With bell transformer No

Extension possible Yes

With socket No

**Standards**

Subject to technical modifications

**Safety**

---

IK protection code against mechanical impacts

IK05

---

Protection class

isol.class I