



JK1B12S2

**125A TPN BOARD, INVICTA, 12WAY, SURFACE, FOR 50 OC TESTING**

**Technical characteristics**

**Configuration**

Number of modules	0
-------------------	---

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Dimensions**

Insertion depth	120 mm
Depth of installed product	125 mm
Internal depth	117 mm
Height of installed product	715 mm
Width of installed product	445 mm
Thickness of sidewall material	1.2 mm

**Cover, door**

Material thickness cover	1.2 mm
Type of door closing	non keylock
Identification of protection index	41
Interlockable	No
Door locking	with special tool
Transparent cover or door	No

**Materials**

Colour	light grey
--------	------------

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Connection**

Number of conduit inlets	26
Number of accessible phases	3

**Equipment**

With energy meter	No
Quantity of rails	0
Can be accessorized	Yes
With bell transformer	No
Extension possible	Yes
With socket	No

**Standards**

Subject to technical modifications

**Safety**

---

IK protection code against mechanical impacts

IK05

---

Protection class

isol.class I